

Posiflex free motion elbow support system



Imagine working with complete freedom of motion but without exertion in your neck, back and shoulder muscles. With superb engineering and unmatched ergonomics, the Posiflex Free Motion Elbow Support System features free moving, height-adjustable elbow supports that follow your every move without restriction, yet provide total support and stability for your arms and shoulders. It is a life-changing innovation that will have you feeling your best and performing your best — guaranteed!

Numerous clinical studies have demonstrated that the use of mobile elbow supports contributes to a more secure and comfortable work posture as muscular contractions in the arms and shoulders are diminished significantly. Based on three years of research and clinical stud-

ies, Posiflex Gel Padded Free Motion Elbow Supports cradle every user's elbows with ideal firmness and comfort while allowing for complete mobility. High-strength design with solid steel components clamps onto the riser of any dental stool in minutes, with wrench provided.

Here is what a few people had to say about the elbow supports:

"After only a short use, my backaches have diminished by about 80 percent. It would be a handicap to not have this equipment. Finally, a product that is designed for the practitioner."

— G. St-Rock DDS,
Montreal, Canada

"I have found that I have far less lower back and neck discomfort and find practicing dentistry far more comfortable. Having the abil-



ity to rest an elbow during static procedures removes a lot of stress from my lower back. I am very happy with my decision to purchase the Posiflex for my associate and myself."

— Ray Katz, DDS,
Ontario, Canada

For more information, visit Posiflex at the Practicon booth, No. 1765, at the CDA Spring Session.

Grandio Seal



Grandio Seal, the first nano-fissure sealant, combines optimal wetting properties with excellent wear and low polymerization shrinkage.

Fissure sealing ranks among the standard repertoire of modern prophylaxis concepts. The choice for sealing, however, is still difficult. Clinicians have to decide between using a pit and fissure sealant with good wetting properties but higher shrinkage and only fair wear characteristics or a flowable composite with better physical values but compromise in wetting properties with the risk that the flowable composite does not penetrate all areas of the fine fissures, which could lead to secondary caries.

Grandio Seal, the first nano-fissure sealant, enables long-term sealing without compromises. VOCO used its proven nano hybrid technology to fill Grandio Seal by 70 percent (weight) without changing the viscosity of traditional sealants. The highest filler degree of all fissure sealants gives Grandio Seal outstanding wear resistance and a reduced shrinkage.

Grandio Seal does not drip and can be precisely applied with the extra thin bendable metal tip allowing access to even the finest fissures and pits. A specially defined pressure point on the syringe provides optimum material flow for exact and even wetting of all pit and fissures. Grandio Seal comes in a white opaque shade for easy visibility.

For more details, contact VOCO at (888) 658-2584, info@voco.com, www.vocoamerica.com or stop by the VOCO booth, No. 576, at the CDA Spring Session.

Shade-X by X-Rite

Shade-X, a new generation of shade taking device from X-Rite, the makers of the award winning ShadeVision system, is the ideal product with an ideal price of less than \$1,000.

In the growing importance of esthetics in the dental industry, X-Rite products take the guesswork out of measuring and communicating the color of teeth.

The emphasis on esthetic dentistry and the ability to create natural-looking restorations has become more important than ever. One of the most important pieces of information to achieve beautiful restorations is the communication of color. Dentists still rely on their own visual acuity to perform shade matching — a completely subjective technique that is prone to numerous errors.

Shade-X is cordless, affordable and accurate and is an easy-to-use system that allows clinicians to accurately capture and communicate tooth shade in less than 0.5 seconds.

The user-friendly format allows clinicians and technicians to easily use, read and interpret shades, immediately, thus eliminating guesswork and inaccurate measurements.

This innovative product is ideal for measuring shades for crowns, bridges, composites and whitening results all at a very low price. The Shade-X supports most widely used shade guides today as well as CAD/CAM block selection.

For more information, visit X-Rite at the Henry Schein booth, No. 2218, during the CDA Spring Session.

